

T80 Toxic Gas Monitor

Features


- Microprocessor based
- 4-20mA Analogue Output
- Voltage free relay contacts
- · RS485 digital interface
- · Alphanumeric dot-matrix display
- · "One Person" calibration
- Gel based electrochemical sensor
- Standalone operation

The Monicon T80 is a high quality, self contained, toxic gas sensor that offers a host of sophisticated features to provide fast, reliable warnings against exposure to dangerous concentrations of toxic gases such as CO, SO₂, H₂S, O₃, NO, NO₂, HCI, HCN, CI₂, and oxygen.

The T80 will operate as a standalone instrument or in conjunction with a controller or a computer. It is housed in an attractive, compact enclosure and may be configured or calibrated by one person.

The gas concentration is indicated on a rugged 8-character alphanumeric display which also indicates instrument status.

The T80 is fully user programmable and is easily calibrated by one person. All user variables are stored in non-volatile memory (EEPROM) and retained indefinitely even during total power failure.





Typical Applications for the T80

- · Boiler houses
- · Car Parks
- Food processing
- Paint manufacture
- Chemical Processing
- · Ventilation Systems
- · Laboratories
- Schools & Colleges
- · Greenhouses Refrigeration

The T80 is a 4-20mA, 3-wire transmitter. It is housed in a rugged, compact metallic enclosure. It incorporates advanced SMT electronics and an amperometric electrochemical sensor based on micro fuel cell technology, designed to be maintenance free and inherently stable.

The sensor uses the highly successful capillary diffusion barrier technology, resulting in a low temperature coefficient and a direct response to concentration, relatively unaffected by pressure. The use of electrodes based on fuel cell technology gives a high reserve of activity which results in long term stability. The sensor is a small plug-in component and is easily replaced in minutes when it becomes depleted.

Gas diffusing to the sensor electrode reacts at the surface of the electrode by reduction (or by oxidation for some sensors). Reactions are catalysed by specially developed electrode materials and are designed to be specific to the gas being sensed.

The unit is calibrated or user-programmed by means of on-board pushbutton switches. The operator is then guided through a variety of options by a user-friendly menu. The CPU constantly verifies system operation. In the unlikely event of a fault, the operator is alerted with a helpful diagnostic display.

T80 Specifications

Supply voltage
Power consumption
Circuit protection
Transient Protection
Analogue output
Analogue output load
Operating temperature

Storage temperature Humidity range

Preconditioning Requirements

Full-Scale range display Response time (T90)

Drift, S.T.P. continuous duty in air

Linearity Repeatability Resolution

Recommended Calibration Interval

Weight

RS485 operating mode Max. units on RS485 loop RS485 comm parameters RS485 error checking

Unit interrogation time

Relay contacts Option setting Alarm setting Alarm types

Recommended calibration flow rate

Mounting holes
User variable storage

Electromagnetic Conformance (EMC)

Cable gland entry

Terminations

Enclosure

Literature supplied

Nominal 24Vdc (operates from 20Vdc to 35Vdc)

2W nominal, 2.3W maximum

Electronic current limiter, 1.5A auto-reset PCB mounted, 3 Joule, Metal Oxide Varistor 4-20mA current source referenced to 0V 100 Ohms typical, 500 Ohms maximum

-20°C to +40°C -40°C to +50°C

10%RH to 90%RH (Non-condensing)

Operational: 30 seconds, Specification: 60 minutes

0-3, 0-5, 0-25, 0-50, 0-100, 0-250 (depends on gas and sensor)

Depends on sensor, e.g. <30 seconds for CO <3% over three months at 20°C (depends on sensor)

±5% ±2%

1%

6 months (depending on application)

1.5Kg (including sensor)

Slave mode, half duplex, polled

100 1200-N-8-1 1 byte checksum

400mS

SPST, NO, 230V @ 1A each for A1 & A2

Digital setting (all options fitted as standard and user selectable)
Digital setting (fully adjustable between 10% and 90% of full scale)
Energised/de-energised. Enrichment/deficiency. User selectable

500mL per minute

4 holes, diam 5mm, spaced 145mm horizontally, 63mm vertically


Non-volatile RAM (EEPROM)

Complies with EN50081 and EN50082

M20 x 1.5

Detatchable, PCB mounted terminal blocks to accept 1.5mm² cable Epoxy coated aluminium. Size W: 160mm H: 100mm D: 60mm

24-page detailed instruction manual with wiring diagram



Monicon Technology Ltd Ballybrit Industrial Estate Monivea Road Galway Ireland

Tel: +353 91 752884 Fax: +353 91 752886 e-mail: sales@monicon.com web-site: www.monicon.com

T80-050710-2